

# Suggested RAL and NCS cross-references for our plain colours

Code	NCS	RAL
<b>005</b>	S 9000-N	9005 (G)
<b>030</b>	S 0502-G50Y	9016 (G)
<b>122</b>	S 4050-B80G	6016 (G)
<b>149</b>	S 2000-N	7035 (G)
<b>156</b>	S 1010-Y30R	1015 (D)
<b>206</b>	S 0505-Y30R	1015 (G)
<b>A 014</b>	S 1010-G	-
<b>A 031</b>	S 0505-Y50R	-
<b>A 036</b>	S1030-G10Y	6019 (G)
<b>A 059</b>	S 0565-R	3017 (D)
<b>A 069</b>	S 4010-Y30R	1019 (G)
<b>A 088</b>	S 6030-R10B	3005 (G)
<b>B 001</b>	S 2065-R90B	5015 (G)
<b>B 004</b>	S 0505-R70B	9003 (G)
<b>B 012</b>	S 0603-G80Y	9010 (G)
<b>B 014</b>	S 0804-Y50R	-
<b>B 015</b>	S 0502-G50Y	9016 (G)
<b>B 018</b>	S 3050-Y70R	-
<b>B 029</b>	S 2005-Y50R	-
<b>B 044</b>	S 0580-Y10R	1003 (G)
<b>B 048</b>	S 1030-R80B	-
<b>B 068</b>	S 0502-G	9016 (G)
<b>B 069</b>	S 0505-R70B	9003 (G)
<b>B 070</b>	S 0500-N	9016 (G)
<b>B 072</b>	S 2010-Y40R	-
<b>B 086</b>	S 4050-R80B	5002(G)
<b>B 097</b>	S 3050-R80B	-
<b>C 001</b>	S 4010-R10B	-
<b>C 017</b>	S 0907-Y30R	1015 (D)
<b>C 018</b>	S 4030-R90B	5023 (G)
<b>C 035</b>	S 6020-G90Y	-
<b>C062</b>	S 1080-Y90R	2002 (G)
<b>C 070</b>	S 7010-Y50R	8025 (G)
<b>C 094</b>	S 2010-B70G	-

Code	NCS	RAL
<b>E 012</b>	S 7005-R80B	7015 (G)
<b>E 021</b>	S 0804-Y30R	9001 (G)
<b>E 026</b>	S 2555-B30G	-
<b>F 001</b>	S 0580-Y60R	2010 (G)
<b>F 006</b>	S 6500-N	7005 (L)
<b>F 007</b>	S 3000-N	7004 (D)
<b>F 008</b>	S 1010-R80B	-
<b>F 017</b>	S 2030-Y40R	-
<b>F 026</b>	S 2005-Y50R	-
<b>G 003</b>	S 3005-R80B	7040 (G)
<b>G 005</b>	S 1030-B	-
<b>G 012</b>	S 1505-Y20R	1013 (D)
<b>G 013</b>	S 4005-R80B	7001 (G)
<b>G 024</b>	S 4050-R	3011 (G)
<b>G 028</b>	S 7502-B	7024 (G)
<b>G 029</b>	S 1502-B	7035 (G)
<b>G 030</b>	S 0570-Y80R	2012 (D)
<b>G 031</b>	S 0560-Y20R	1003 (G)
<b>G 033</b>	S 4005-R80B	7001 (G)
<b>G 044</b>	S 2000-N	7047 (G)
<b>G 059</b>	S 7502-B	7024 (G)
<b>H 014</b>	S 1080-R	3018 (G)
<b>J 001</b>	S 0570-G90Y	1018 (G)
<b>J 016</b>	S 1040-Y10R	-
<b>J 017</b>	S 0540-G80Y	-
<b>J 018</b>	S 1050-Y10R	-
<b>K 001</b>	S 0530-G40Y	-
<b>K 003</b>	S 4020-G70Y	6013 (D)
<b>L 005</b>	S 1005-Y70R	-
<b>L 026</b>	S 1030-B50G	6027 (G)
<b>L 027</b>	S 3020-R70B	-
<b>M 017</b>	S 1505-Y10R	1013 (D)
<b>M 024</b>	S 8005-Y50R	8028 (G)
<b>M 047</b>	S 3020-B70G	-

Code	NCS	RAL
<b>M 092</b>	S 3050-R80B	-
<b>N 001</b>	S 0580-Y40R	2003 (D)
<b>N 002</b>	S 2040-G80Y	-
<b>N 005</b>	S 9000-N	9005 (G)
<b>O 022</b>	S 1015-R90B	-
<b>O 031</b>	S 2020-G80Y	1000 (L)
<b>O 054</b>	S 2020-Y40R	-
<b>P 001</b>	S 5005-Y20R	7006 (D)
<b>P 002</b>	S 8010-R70B	5011 (G)
<b>P 003</b>	S 1020-R70B	-
<b>P 016</b>	S 2040-R80B	-
<b>P 043</b>	S 0520-Y10R	-
<b>P 044</b>	S 0515-Y30R	-
<b>P 045</b>	S 0520-G30Y	-
<b>P 053</b>	S 0907-R10B	-
<b>P 060</b>	S 2030-R60B	-
<b>P 070</b>	S 3040-G90Y	-
<b>P 076</b>	S 1020-Y30R	1001 (L)
<b>P 080</b>	S 2030-R50B	-
<b>P 092</b>	S 1060-G80Y	-
<b>R 001</b>	S 1080-Y90Y	3020 (G)
<b>R 021</b>	S 1515-R40B	-
<b>R 036</b>	S 2570-Y90R	3001 (G)
<b>R 043</b>	S 5040-Y90R	3009 (G)
<b>S 011</b>	S 2060-Y50R	2000 (G)
<b>S 018</b>	S 6020-R70B	-
<b>T 005</b>	S 2050-B70G	-
<b>T 007</b>	S 0530-G60Y	-
<b>U 001</b>	S 1010-Y30R	1015 (G)
<b>V 011</b>	S 0520-B30G	-
<b>V 013</b>	S 3050-G20Y	6017 (D)
<b>V 014</b>	S 1060-R30B	2011 (D)
<b>Y 022</b>	S 2060-R30B	-